



Toyo Seiki Seisaku-sho, Ltd. 5-15-4, Takinogawa, Kita-ku, Tokyo 114-8557, Japan

## No.168 Digi-Bekk Smoothness Tester Model **DB-2**



### ■ APPLICATION

The **Digi-Bekk Smoothness Tester** evaluates smoothness from the rate at which air leaks out from the space in between the surface of sample (put in contact with a smooth glass surface) and the smooth glass surface.

## ■ SPECIFICATIONS

Model	DB-2
Indication of vacuum	0 to 55.00kPa
Attainable of vacuum	55kPa
Vacuum setting	0.01kPa steps
Power requirement	Single-phase, AC100V, 50Hz or 60Hz, 0.2kVA
Dimensions	W510 x D320 x H390mm
Weight	Approx. 28kg
Related standard	JIS P 8119

*Specifications are subject to change without notice.*

---



**TOYO SEIKI SEISAKU-SHO, LTD.**

5-15-4, Takinogawa, Kita-ku, Tokyo 114-8557, Japan

Tel:+81-3-3916-8183 Fax:+81-3-3916-8173

[www.toyoseiki.co.jp](http://www.toyoseiki.co.jp)

20191203 MN